


AIRHUG

2K HD WEBCAM


User Manual




AIRHUG 11

KNOW YOUR PRODUCT


LED activity light HD lens




Privacy cover switch
(Slide to the left
open the lens)




Privacy cover switch
(Slide to the right
close the lens)



Microphone




Tripod thread for
 $\frac{1}{4}$ inch screw
(Tripod not provided)



USB-A cable

Adjustable clip/stand

WHAT'S IN THE BOX



Webcam with attached
USB-A cable ×1




User manual ×1

Setting Up the Webcam


Option A: Mounting on a Monitor/Laptop

1. Place your webcam on a computer, laptop or monitor at a position or angle you desire.
2. Adjust the webcam to make sure the end on the universal mounting clip is flush with the back of your device.
3. Manually adjust the webcam up/down to the best position to frame yourself.




Option B: Placing on Desktop

Fold in the clip so it forms a flat surface, and place it on a flat desk top.



Option C: Mounting on a Tripod


With the clip folded in, mount the webcam onto a tripod (not provided) with the ¼ inch thread.



Connecting to Computer

1. Plug the USB-A connector into the USB-A port on your computer.

- * Plug-and-play support will let your computer instantly recognize the webcam.
- * If your computer does not instantly recognize the webcam, try plugging into a different USB port or restart the computer.



2. Open the app you want to use with the webcam.

- * LED activity light will light up when the webcam is in use by an app.

You may need to manually select this webcam and its built-in microphones for your PC system or software.

A) Windows System

1. Go to Settings > Privacy > Camera and turn on "Allow apps to access your camera".
2. Turn on each of the listed apps where you want to use the camera. After you open the Camera app, you may need to switch to the Full HD Camera.

B) macOS System

1. Go to the Apple menu > System Preferences > Security & Privacy, then choose Camera from the list on the left side.
2. Locate the app(s) you want to enable camera access for and check the box alongside that app name to enable camera access for that application.

C) Software (Zoom or more)

Go to Settings > Video > Camera and choose this webcam.

Specifications

Specifications are subject to change without notice.

Charge input	5V $\overline{\text{---}}$ 500mA
Resolution	2592x1944 2560x1440 1920x1080 1280x720
Horizontal FOV	71°
Focus type	Auto Focus
Voice Pickup Distance	2m
Sensor	5MP CMOS (1/3')
Focus distance	30cm ~ ∞
Maximum video frame rate	30fps
Video codec	MJPEG
Supported Operating Systems or Software	Windows 7 / 8 / 10 / 11 MAC OS X
Microphone	Dual stereo microphones
Height x Width x Depth	3.2 in x 1.8 in x 1.6 in 82mm x 48mm x 42.4mm
Cable Length	5.2ft (1.6m)
Weight:	2.6 oz (75 g), including clip and cable

Manufactured by/ Hergestellt von/ 製：
Feifan Innovation E-commerce Shenzhen Limited
Baoyunda Logistics Center Building 3-602
Fuhua Community, Xixiang Street, Baoan District
Shenzhen, Guangdong, China 518000
Email: info@airhugshop.com
Phone / Telefon/ 電話: 0086-13810899914

Like Sun GmbH
Planckstr. 59, 45147 Essen, Germany
Contact Person: Ke Li
Telefon: +49 471 39156605
Email: ec-connection@web.de



Name: KOVA ASSOCIATES LTD
Address: 72a Kingston Road, Portsmouth,
Hampshire, PO2 7PA, United Kingdom
Contact Person: Louisa Timms
Tel: 0044 (0) 23 8097 0315
E-mail: KOVA.Compliance@outlook.com



Made in China

In China hergestellt

中国製